



LEGEND:

1. FIRE RATED FRAME.
2. FIRE RATED DOOR w/ VISION LITE. (OPTIONAL)
3. HINGES 4 1/2" X 4 1/2" HEAVY WEIGHT.
4. MORTISE LOCK.
5. FLAT HEAD SCREWS. SCREW ANCHORS TO DRILL AND TAP INTO STEEL DECKING.
6. MOUNTING BOLTS. (OPTIONAL FILLET WELD-SECTION B-B)
7. 1/4" THICK THRESHOLD. (OPTIONS ARE 304-2B OR MILD STEEL)
8. FIRE RESISTANT GLASS, FACTORY INSTALLED IN DOOR.
9. MOUNTING BOLTS OR FILLET WELD TO STEEL BULK HEAD. (ENSURE COMPATIBLE MATERIALS)
10. WELD TO STEEL DECKING.

NOTES:

- DOOR HAS 1/4" UNDERCUT. (SILL OPTIONS 1 & 2)
- MATERIAL OPTIONS: STAINLESS STEEL OR GALV. STEEL.
- INSTALLATION OPTION:

SEE OPTION #1 OR #2 BELOW.
 - OPTIONAL WINDOW SUPPLIED IN ONE SIZE ONLY.