


A 01 Ella Marie Double Estate Gate

Shown As Residential Series

Scale: NTS

*Displayed As Standard



Bad Ass

Adjustable: 3.0625" to 3.25"

Bad Ass

Adjustable: Hybrid 3.0625" to 3.25"


Block

Fixed: 3.25"




J-Bolt

Adjustable: 3.25" to 6.50"



Scalloped



Bell



Sunrise

GATE OPENING

End Uprights

Bottom Member

Corner Gussets

Truss Cables

Double

*12'-1" to 23'-11"

2" x 3" x 1/8"

2" x 3" x 1/8"

NONE

NONE

24'-0" to 27'-11"

2" x 3" x 1/8"

2" x 4" x 1/8"

Yes

NONE

28'-0" to 32'-0"

2" x 3" x 1/8"

2" x 6" x 1/8"

Yes

Yes

32'-1" to 40'-0"

2" x 3" x 1/8"

Custom

NONE

NONE

*Any gate opening under 12'-1", will require a Estate Gate upcharge for listed specifications.

A 03 Material Specification Chart

Double Swing Estate Gate

A 04 Arch Options

All Considered Standard

Scale: NTS

*Arch Follows 1" Of Rise For Every Foot Of Opening

DRAWING NOTES:

We kindly ask that you do not scale directly from the drawings. We recommend consulting our Fence and Gate Style Sheet for further options. Please be aware that while additional gate hardware is available, its use may impact the clearances for hinges and latches.

Customer Signature:

Ella Marie Double Estate Gate

4 Rail - Residential Series - Puppy Picket

(Standard Gate With The Optional Puppy Picket)

4-Rail System Required For Gates Starting At 7'-0" High

Checked By: Antebellum

Order #:

Drawn By: J. Mixon

Drawn Date: 21-Nov-25

ANTEBELLUM
Manufacturing

DO NOT SCALE DRAWING, FOR DIMENSIONS NOT SHOWN

CONTACT PLAN COORDINATOR FOR CLARIFICATION

2399 NW 35th St, Ocala, FL 34475

Ph: 352.877.3888

Em: Info@AntebellumMFG.Com



Triad



Quad



Fleur De Lis