


**A** Sydney Single Estate Gate  
01 Shown As Commercial Series Scale: NTS  
\*Displayed As Standard



**Bad Ass**  
Adjustable:  
3.0625" to 3.25"

**Bad Ass**  
Adjustable: Hybrid  
3.0625" to 3.25"

**Block**  
Fixed: 3.25"

**J-Bolt**  
Adjustable:  
3.25" to 6.50"

**A** Estate Hinges Options  
02 To Fit 4" & 6" Post Scale: NTS  
\*Standard Deduction Is 3 1/4" For These Hinges

GATE OPENING	End Uprights	Bottom Member	Corner Gussets	Truss Cables
<b>Single</b>	<b>Uprights</b>	<b>Bottom Member</b>	<b>Corner Gussets</b>	<b>Truss Cables</b>
*6'-0 1/2" to 11'-11 1/2"	2" x 3" x 1/8"	2" x 3" x 1/8"	NONE	NONE
12'-0" to 13'-11 1/2"	2" x 3" x 1/8"	2" x 4" x 1/8"	Yes	NONE
14'-0" to 16'-0"	2" x 3" x 1/8"	2" x 6" x 1/8"	Yes	Yes
16'-0 1/2" to 20'-0"	2" x 3" x 1/8"	Custom	NONE	NONE

\*Any gate opening under 6'-0 1/2", will require a Estate Gate upcharge for listed specifications.

**A** Material Specification Chart  
03 Single Swing Estate Gate

## Sydney Single Estate Gate

3 Rail - Commercial Series - Puppy Picket  
(Standard Gate With The Optional Puppy Picket)

3-Rail System Designed For Gates Up To 6'-0" High

Checked By: Antebellum

Order #:

Drawn By: J. Mixon

Drawn Date: 24-Nov-25


**ANTEBELLUM**  
Manufacturing

DO NOT SCALE DRAWING. FOR DIMENSIONS NOT SHOWN  
CONTACT PLAN COORDINATOR FOR CLARIFICATION


2399 NW 35th St, Ocala, FL 34475

Ph: 352.877.3888

Em: Info@AntebellumMFG.Com



**A** Rings  
04 Welded To Pickets Scale: NTS



**A** Butterfly Scrolls  
05 Shown Every Other Picket Scale: NTS  
\*Optional Butterfly Scrolls On Every Picket



**A** Finials  
06 Screwed To Pickets Scale: NTS

### DRAWING NOTES:

We kindly ask that you do not scale directly from the drawings. We recommend consulting our Fence and Gate Style Sheet for further options. Please be aware that while additional gate hardware is available, its use may impact the clearances for hinges and latches.

Customer Signature: