


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SUNCOR STAINLESS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF SUNCOR STAINLESS IS PROHIBITED.


| REVISIONS | | | |
|-----------|----------------|---------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | SAMPLE DRAWING | X/XX/XX | XX |



NOTES:

- HAND RAIL SYSTEM CONSISTING OF SUNRAIL LATITUDE STYLE WITH HORIZONTAL WIRE ROPE.
- DRAWING AND DIMENSIONS BASED UPON CUSTOMER SUPPLIED DRAWINGS
- ALL DIMENSIONS AND RAILING DETAILS ARE PENDING CUSTOMER APPROVAL
- 36" HAND RAIL SYSTEM CONSISTING OF 2" DIA BRUSHED 16 GAUGE 316 SS TUBING, CAST 316 SS FITTINGS, EPOXY CONNECTIONS AT JOINTS

Deck or mounting area and stair dimensions MUST be confirmed by the customer and or contractor. Suncor/Atlantis rail will NOT be responsible for errors or misinterpretations of the railing system designed by us based upon customer confirmed dimensions. Additional drawing time to change the design or correct for errors after signing will result in additional costs as well as any changes to parts made per the drawing. Carefully review the drawing before signing and accepting.



ASSEMBLY NOTE:
PLEASE TAKE CARE TO ORIENTATE POSTS SO THAT TENSIONERS GO TO SWIVELS. DO NOT ORIENTATE SWIVELS TO SWIVELS.

CUSTOMER SIGNATURE: _____ **DATE:** _____

| | | | |
|---|----------|--|------------|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES (DIMENSIONS ARE IN MILLIMETERS) | | CAD GENERATED DRAWING DO NOT MANUALLY UPDATE | |
| FRACTIONS | DECIMALS | ANGLES | |
| 1/16" | .0625 | ±1/2° | |
| 1/32" | .03125 | ±1/4° | |
| 3/64" | .046875 | ±1/8° | |
| MATERIAL | | APPROVALS | DATE |
| 316SS | | DRAWN | XX X/XX/XX |
| FINISH | | CHECKED | |
| BRUSHED | | RESP ENG | |
| | | MFG ENG | |
| | | QUAL ENG | |

| | | | |
|---|----------|-----------|------------|
| ATLANTIS RAIL SYSTEMS | | | |
| ATLANTIS LATITUDE RADIUS SAMPLE DRAWING | | | |
| SIZE | FSCM NO. | ORDER NO. | REV |
| D | | XXXXXX | A |
| SCALE | NTS | CAD FILE | XXXXXXXXXX |
| | | | SHEET |