Solare[™] Acoustic Single Glazed Partition System Free Swing Hinge





Solare[™] Acoustic Single Glazed Partition System Characteristics

Maximum Glazing Panel Width: 60" max. (custom widths available upon request)

Maximum Glazing Panel Height: Full height up to 12 feet

Glazing Available: 3/8" Clear tempered, 7/16" Clear laminated, 1/2" Clear tempered, 9/16" Clear laminated, Lunar™ Smart Glass privacy glazing, 3/4" glazing is available

Available Glazing Types: Clear Tempered, Low Iron, Laminated, Lunar Smart Glass™

Door Width: 38" max. (custom larger widths available upon request)

STC Rating: 35

Material: Stainless Steel; ASTM A276, Type 304.

Hinge Standard: 2 Hinges to 90" high, 3 Hinges to 108" high, 4 Hinges to 180" high



200 Pemberwick Road Greenwich, CT 06831
 T:
 (877) 282-6843

 F:
 (914) 934-5992

 W:
 www.avantisystemsusa.com

 E:
 sales@avantisystemsusa.com

1