



**ASSA ABLOY**

ASSA ABLOY Entrance Systems  
1900 Airport Road  
Monroe, NC 28110  
Phone: 1-866-BESAM-87  
specdesk.na.aes@assaabloy.com

ASSA ABLOY RD3-100 MANUAL  
REVOLVING DOOR  
PLAN VIEW



BREAKAWAY POSITION

MODEL #	TOTAL DIAMETER "DT"	INSIDE DIAMETER "D"	ROUGH OPENING "RO"	THROAT OPENING "TW"	OVERALL FRAME HEIGHT "OFH"
RD3-100-6	74"	70 7/8"	74 15/16"	31 7/32"	94 1/2"
RD3-100-7	85 13/16"	82 11/16"	86 3/4"	37 1/8"	94 1/2"
RD3-100-8	97 5/8"	94 1/2"	98 3/4"	43 1/32"	94 1/2"

NOTE: FOR SPECIAL HEIGHT PACKAGES CONTACT FACTORY

DWG NO. RD3-100		SHEET 1 OF 2	
DRN BY M.H.W.	DATE 10/4/13	CHK BY	DATE 5/30/14
		REV. A	DATE
ASSA ABLOY RD3-100 MANUAL REVOLVING DOOR PLAN VIEW			
<b>ASSA ABLOY</b>		ASSA ABLOY Entrance Systems 1900 Airport Road Monroe, NC 28110 Phone: 1-866-BESAM-87 specdesk.na.aes@assaabloy.com	