



ASSA ABLOY RD4-100 MANUAL
 REVOLVING DOOR
 PLAN VIEW



MODEL #	TOTAL DIAMETER "DT"	INSIDE DIAMETER "D"	ROUGH OPENING "RO"	THROAT OPENING "TW"	OVERALL FRAME HEIGHT "OFH"
RD4-100-6	74"	70 7/8"	74 15/16"	46 7/8"	94 1/2"
RD4-100-7	85 13/16"	82 11/16"	86 3/4"	55 1/4"	94 1/2"
RD4-100-8	97 5/8"	94 1/2"	98 3/4"	63 9/16"	94 1/2"

NOTE: FOR SPECIAL HEIGHT PACKAGES CONTACT FACTORY

DWG NO. RD4-100		SHEET 1 OF 2	
DRN BY M.H.W.	DATE 10/4/13	CHK BY	DATE 10-06-16
ASSA ABLOY RD4-100 MANUAL REVOLVING DOOR PLAN VIEW			
ASSA ABLOY		ASSA ABLOY Entrance Systems 1900 Airport Road Monroe, NC 28110 Phone: 1-866-BESAM-87 specdesk.na.aaes@assaabloy.com	