



- NOTES:** UNLESS OTHERWISE SPECIFIED
1. DIMENSIONS ARE IN INCHES (MM).
 2. MACHINED SURFACES TO BE 63 μ IN MAX.
 3. DO NOT SCALE DRAWING.
 4. PART TO BE FREE OF BURRS AND SHARP EDGES.
 5. ALL MATERIAL TO BE CLEAN, DEGREASED AND FREE OF ALL IMPURITIES.
 6. ANY CHANGE MUST BE AUTHORIZED BY AN SC&R ENGINEER.

MATERIAL TYPE: 316 SS
 VENDOR ID:

REV	DATE	DESCRIPTION OF CHANGE	ECN	BY	APPV
REVISIONS					
	Stainless Cable & Railing TOLERANCES XX ±.01 XXX ±.005 ANGULAR .45° FRACTIONAL 1/32		THIS DRAWING IS THE PROPERTY OF SC&R. IT IS TO BE USED ONLY FOR THE PROJECT AND IN THE MANNER SPECIFIED HEREIN. NO PART OF THIS DRAWING IS TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN PERMISSION OF SC&R.	2" Stainless Tubing	
	Dwg No 05-300-01	SHEET 1 OF 1			
DRN BY GH	DATE 1/9/2011	PROJ:			