



NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES (MM).
2. MACHINED SURFACES TO BE 63 μ IN MAX.
3. DO NOT SCALE DRAWING.
4. PART TO BE FREE OF BURRS AND SHARP EDGES.
5. ALL MATERIAL TO BE CLEAN, DEGREASED AND FREE OF ALL IMPURITIES.
6. ANY CHANGE MUST BE AUTHORIZED BY AN SC&R ENGINEER.

MATERIAL TYPE: 316 SS

VENDOR ID:

REV	DATE	DESCRIPTION OF CHANGE	REVISIONS		ECN	BY	APPV	
SC & R		Stainless Cable Railing	XX 4.00	TOLERANCES UNLESS OTHERWISE SPECIFIED				
			XXX 3.005	UNLESS OTHERWISE SPECIFIED				
			ANGULAR .045°					
			FRACTIONAL 1/32					
05	1/8/2011							
			THIS DRAWING IS THE PROPERTY OF SC&R RAILING. IT IS TO BE USED ONLY FOR THE PROJECT SPECIFICALLY IDENTIFIED HEREON. IT IS NOT TO BE REPRODUCED, COPIED, OR IN ANY MANNER USED FOR ANY OTHER PROJECT WITHOUT THE WRITTEN PERMISSION OF SC&R RAILING.		Part: Stainless 2" Post Cap Fixed - Radius Saddle Dwg No: 05-210-01			SHEET 1 OF 1