



DIMENSIONS		cm	
(A)	6"	15	TO
	9"	23	
(B)	2"	5	MIN.
(C)	3"	7.5	MAX.

NOTES:

1. A HEAT GUN MUST BE USED WHEN FORMING PRESSURE-SENSITIVE ELASTOFORM FLASHING IN COLDER TEMPERATURES.
2. FOR PROJECTS WITH 25 & 30-YEAR WARRANTIES OR WHEN USING 90-MIL MEMBRANE, REFER TO [DETAIL U-15G.1](#) FOR REQUIRED FLASHING ENHANCEMENTS.



OUTSIDE CORNER WITH
PRESSURE-SENSITIVE ELASTOFORM
FLASHING (2 PIECE)

MAXIMUM WARRANTY: 20 YEARS



DETAIL NO.

U-15F

THERMOSET UNIVERSAL