


REVISION STATUS - ALL SHEETS ARE THE SAME REVISION				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	X1	DEVELOPMENT	02/28/2017	KRH

NOTES: UNLESS OTHERWISE SPECIFIED

- 1 MATERIAL: MATERIAL SPECIFIED AT INDIVIDUAL PART LEVEL
- 2 ALL DIMENSIONS ARE TO THEORETICAL SHARP.
- 3 REMOVE BURRS AND BREAK ALL SHARP EDGES .03 MAX.
- 4 ALL DIMENSIONS ARE IN INCHES UNLESS STATED OTHERWISE.
- 5 PARTS SHALL BE FREE OF GREASE AND CUTTING FLUID.
- 6 POWDER COAT PER MIL-PRF-24712A (TYPE 3, CLASS 3)

ISOMETRIC VIEW  
FOR REFERENCE ONLY



CONFIGURATION TABLE	
	"A"
IB-16	16.00
IB-17	17.00
IB-18	18.00
IB-19	19.00
IB-20	20.00
IB-21	21.00
IB-22	22.00
IB-23	23.00
IB-24	24.00
IB-25	25.00
IB-26	26.00
IB-27	27.00
IB-28	28.00
IB-29	29.00
IB-30	30.00
IB-31	31.00
IB-32	32.00
IB-33	33.00
IB-34	34.00
IB-35	35.00
IB-36	36.00
IB-37	37.00
IB-38	38.00
IB-39	39.00
IB-40	40.00
IB-41	41.00
IB-42	42.00
IB-43	43.00
IB-44	44.00
IB-45	45.00
IB-46	46.00
IB-47	47.00
IB-48	48.00

RELEASED

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES	ENGINEER		
	ENGINEER		
TOLERANCES ARE:	CHECKED	CAS	02/28/2017
	DRAWN	KRH	02/28/2017
ANGLES	MANAGER APPROVAL		DRAWING TITLE
.XX ± .01 .XXX ± .005			
INTERPRET DRAWINGS IN ACCORDANCE WITH:	THE INFORMATION ON THIS DRAWING IS PROPRIETARY AND SHALL NOT BE DISCLOSED, USED, OR DUPLICATED FOR PROCUREMENT OR MANUFACTURING PURPOSES WITHOUT THE EXPRESS WRITTEN CONSENT OF CENTERLINE STEEL, LLC		SIZE
	ASME Y14.100 ENGINEERING DRAWING PRACTICES ASME Y14.38 ABBREVIATIONS ASME Y14.5 DIMENSIONING AND TOLERANCING ASME Y14.6 SCREW THREAD REPRESENTATION ASME Y14.8 CASTINGS, FORGINGS & MOLDED PARTS AWS A2.4 WELDING SYMBOLS IEEE STD 315 SYMBOLS FOR ELECTRICAL AND ELECTRONIC DIAGRAMS	THIRD ANGLE PROJECTION	
USED ON APPLICATION			CAGE CODE
	SCALE 1:1		DRAWING NO
	SHEET 1 OF 2		IB
			REV X1

8

7

6

5

4

3

2

1

BOM TABLE

ITEM NO.	PART NUMBER	IB-16 QTY.	IB-17 QTY.	IB-18 QTY.	IB-19 QTY.	IB-20 QTY.	IB-21 QTY.	IB-22 QTY.	IB-23 QTY.	IB-24 QTY.	IB-25 QTY.	IB-26 QTY.	IB-27 QTY.	IB-28 QTY.	IB-29 QTY.	IB-30 QTY.	IB-31 QTY.	IB-32 QTY.	IB-33 QTY.	IB-34 QTY.	IB-35 QTY.	IB-36 QTY.	IB-37 QTY.	IB-38 QTY.	IB-39 QTY.	IB-40 QTY.	IB-41 QTY.	IB-42 QTY.	IB-43 QTY.	IB-44 QTY.	IB-45 QTY.	IB-46 QTY.	IB-47 QTY.	IB-48 QTY.
1	A-IB	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
2	H10H-15.75	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
3	H10H-16.75	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
4	H10H-17.75	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
5	H10H-18.75	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
6	H10H-19.75	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
7	H10H-20.75	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
8	H10H-21.75	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
9	H10H-22.75	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
10	H10H-23.75	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
11	H10H-24.75	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
12	H10H-25.75	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
13	H10H-26.75	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
14	H10H-27.75	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
15	H10H-28.75	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
16	H10H-29.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
17	H10H-30.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
18	H10H-31.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
19	H10H-32.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
20	H10H-33.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-
21	H10H-34.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-	-
22	H10H-35.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-	-
23	H10H-36.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-	-
24	H10H-37.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-
25	H10H-38.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-	-
26	H10H-39.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-	-
27	H10H-40.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-	-
28	H10H-41.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-	-
29	H10H-42.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-	-
30	H10H-43.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-	-
31	H10H-44.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-	-
32	H10H-45.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-	-
33	H10H-46.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	-	-
34	H10H-47.75	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1

SIZE	CAGE CODE	DRAWING NO	REV
D		IB	X1
SCALE	1:1	SHEET 2 OF 2	

8

7

6

5

4

3

2

MULTI SHEET

1