

- 1) THE MAXIMUM UNSUPPORTED LENGTH FOR EACH LEG IS 3'-0" (.91m). TYPE "X" AND "Y" HORIZONTAL ONLY.
- 2) THE MINIMUM LENGTH FOR EACH LEG IS 7" (178mm) @ 3" (76mm) PANELS. SHOP FORMED CORNER ONLY.
- 3) SHOP FORMED CORNERS ARE AVAILABLE WITH EACH LEG UP TO 40" (1016mm) MAXIMUM.

PANEL SUPPORT DESIGNED TO PROJECT SPECIFICATIONS

IMV INSERT
(OPTIONAL 3"-T GASKET AVAILABLE)

SEALANT

CLOSURE FLASH
W/SEALANT

SHOP FORMED
CORNER PANEL

3"

[76]

5/8"

[16]

MINIMUM and MAXIMUM
SEE NOTES #2 and #3

6" MIN.

"Y"

SEE Note #1

5/8"
[16]

DETAIL 9

3"-TG IMV OUTSIDE CORNER - SHOP FORMED

*DETAILS SHOWN ARE FOR PROMOTIONAL USE ONLY.
THESE DETAILS SHOULD NOT FOR ANY REASON BE
USED FOR CONSTRUCTION PURPOSES.



CENTRIA

HORIZONTAL APPLICATION