


<p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-10A</p>	<p>3" [76]</p> <p>6" [152]</p> <p>3" [76]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-11A</p>	<p>3 3/4" [95]</p> <p>4 1/2" [114]</p> <p>3 3/4" [95]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-12A</p>	<p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-13A</p>	
<p>6" [152]</p> <p>6" [152]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-14A</p>	<p>3" [76]</p> <p>3" [76]</p> <p>3" [76]</p> <p>3" [76]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-15A</p>	<p>6" [152]</p> <p>6" [152]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-20A</p>	<p>6" [152]</p> <p>3" [76]</p> <p>3" [76]</p> <p>3" [76]</p> <p>3" [76]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-21A</p>	
<p>10" [254]</p> <p>2" [51]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-30A</p>	<p>10" [254]</p> <p>2" [51]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-31A</p>	<p>11" [279]</p> <p>1" [25]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-40A</p>	<p>11" [279]</p> <p>1" [25]</p> <p>Exterior</p> <p>12" [305]</p> <p>1 1/2" [38]</p> <p>IW-41A</p>	
 <p>CENTRIA CENTRIA Architectural Systems</p>			<p>IW SERIES PANELS HORIZONTAL APPLICATION</p>	<p>page IWH-02 Aug. 11</p>