


# CBP Model DL

Dual Bullet and Fire Resistant Door and Frame


UL 752 Listed Level 4 or 8 and UL 10B 3hr  
Fire/Hose Stream Test Listed Flush Door  
Assembly

(A label bearing certification is affixed to the protected side of the frame)


STANDARD FRAME PROFILE: 2" X 5.5"



**THREAT SIDE ELEVATION**



**SECTION VIEW**



**PLAN VIEW**

**CONFIGURATIONS:**

- CUSTOM SIZES UP TO 3'-6" x 8'
- PAIR DOORS (LEVEL 4 ONLY)

**DOORS:**

- ALL WELDED CONSTRUCTION
- 1-3/4" THICK

**FRAME:**

- DOUBLE RABBET PROFILE: 2" X 5-1/2"
- MITERED AND WELDED CORNERS
- SUPPLIED WITH SIX "T"-STRAP ANCHORS

**STANDARD HARDWARE PACKAGE:**

- SARGENT 8204 x LNJ x US26D  
STOREROOM FUNCTION MORTISE LEVER  
LOCKSET
- YALE 4400 x 689 HEAVY DUTY CLOSER
- CBP #12252 BULLET RESISTANT  
CONTINUOUS HINGE
- SILENCERS
- "T"-STRAP ANCHORS

**OTHER HARDWARE OPTIONS:**

- PREP ONLY FOR HARDWARE BY OTHERS
- THRESHOLD AND WEATHERSTRIP
- PREP FOR BOLT OR SCREW ANCHORS

FILE NO. BP1942 SECURITY	
	CHICAGO BULLET PROOF SYSTEMS, INC 2595 BOND ST. UNIVERSITY PARK, IL. 60484 708-534-9102 WWW.CHICAGOBULLETPROOF.COM

## DL DOOR/FRAME

MATERIAL: SHOT-TEX	FINISH: PRIME PAINTED, POWDER COATED, OR STAINLESS STEEL				
DWG. NO.: DL	REVISION: 0	UL LEVEL: 4 OR 8	GLAZING: FLUSH	TOLERANCES: +1/16"	SCALE: 1-1
SHEET: 1 OF 1	WEIGHT: TBD				