



# CUSTOM SIZES AVAILABLE:

CONTACT CBP FOR SIZE AND HARDWARE RESTRICTIONS




**THREAT SIDE ELEVATION**

STANDARD FRAME PROFILE: 2" X 5.5"  
(CUSTOM SIZES AVAILABLE)



**SECTION VIEW**



**PLAN VIEW**

# CBP Model DR

Bullet Resistant Door and Frame

UL 752 Listed and Labeled Levels 1-4, 6 & 8  
Series DL

-Flush door and frame assembly  
-UL 752 Listed Level 4 or 8 and UL 10B  
Listed 3 hour Fire/Hose stream test

(A label bearing certification is affixed to the protected side of the frame)

**CONFIGURATIONS:**

- CUSTOM SIZES UP TO 4' x 10'
- PAIR DOORS
- VISION PANELS
  - \*22"W x 35"H HALF LITE
  - \*22"W x 69"H FULL LITE
  - \*OTHER CUSTOM SIZES
- SLIDING ASSEMBLIES

**DOORS:**

- ALL WELDED CONSTRUCTION
- 1-3/4" THICK
- AVAILABLE WITH WOOD VENEER

**FRAME:**

- DOUBLE RABBET PROFILE: 2" X 5-1/2"
- MITERED AND WELDED CORNERS
- SUPPLIED WITH SIX "T"-STRAP ANCHORS
- CLAMP-ON FRAMES ALSO AVAILABLE FOR WALLS 7-1/2" TO 12" THICK



**STANDARD HARDWARE PACKAGE:**

- SARGENT 8204 x LNJ x US26D STOREROOM FUNCTION MORTISE LEVER LOCKSET
- YALE 4400 x 689 HEAVY DUTY CLOSER
- CBP #12252 BULLET RESISTANT CONTINUOUS HINGE
- SILENCERS
- "T"-STRAP ANCHORS

**OTHER HARDWARE OPTIONS:**

- PREP ONLY FOR HARDWARE BY OTHERS
- BATT FIBERGLASS INSULATION
- THRESHOLD AND WEATHERSTRIP
- PREP FOR BOLT OR SCREW ANCHORS
- UL 752 LISTED VENTILATION LOUVRE AVAILABLE FOR LEVELS 1-4: LVU SERIES LOUVRE PANEL 24"W x 12"H

FILE NO. BP1942  
SECURITY

CHICAGO BULLET PROOF SYSTEMS, INC  
2595 BOND ST. UNIVERSITY PARK, IL. 60484  
708-534-9102  
WWW.CHICAGOBULLETPROOF.COM

## DR DOOR/FRAME

MATERIAL: SHOT-TEX FINISH: PRIME PAINTED, POWDER COATED, OR STAINLESS STEEL

DWG. NO.: DR	REVISION: 0	UL LEVEL: 1-4, 6 & 8	GLAZING: TBD	TOLERANCES: +/-1/16"	SCALE: 1-1
--------------	-------------	----------------------	--------------	----------------------	------------

SHEET: 1 OF 1	WEIGHT: TBD
---------------	-------------