

CBP Model DT

Detention Door and Frame

UL 752 Listed and Labeled Levels 1-4, 6 & 8

Ballistic certification is only available without food pass assembly

CONFIGURATIONS:

- CUSTOM SIZES UP TO 4' x 10'
- PAIR DOORS
- VISION PANELS
- SLIDING ASSEMBLIES

DOORS:

- ALL WELDED CONSTRUCTION
- 1-3/4" THICK

FRAME:

- DOUBLE RABBET PROFILE: 2" X 5-1/2"
- MITERED AND WELDED CORNERS
- SUPPLIED WITH SIX "T"-STRAP ANCHORS
- CLAMP-ON FRAMES ALSO AVAILABLE FOR WALLS 7-1/2" TO 12" THICK


STANDARD HARDWARE PACKAGE:

- SOUTHERN FOLGER 1070A COMBINATION SPRING AND DEADLOCK & 470C BOLT KEEPER/STRIKE
- YALE 4400 x 689 HEAVY DUTY CLOSER
- FOLGER ADAM NO. 4 FLUSH PULL
- CBP #12252 BULLET RESISTANT CONTINUOUS HINGE
- SILENCERS
- "T"-STRAP ANCHORS


OTHER HARDWARE OPTIONS:

- SOUTHERN FOLGER NO. 262 FOOD PASS ASSEMBLY
- PREP ONLY FOR HARDWARE BY OTHERS
- BATT FIBERGLASS INSULATION
- THRESHOLD AND WEATHERSTRIP
- PREP FOR BOLT OR SCREW ANCHORS
- UL 752 LISTED VENTILATION LOUVRE AVAILABLE FOR LEVELS 1-4: LVU SERIES LOUVRE PANEL 24"W x 12"H


STANDARD FRAME PROFILE: 2" X 5.5"



SECTION VIEW





PLAN VIEW



THREAT SIDE ELEVATION

SHOWS OPTIONAL FOOD PASS ASSEMBLY

FILE NO. BP1942
SECURITY

CHICAGO BULLET PROOF SYSTEMS, INC
2595 BOND ST. UNIVERSITY PARK, IL. 60484
708-534-9102
WWW.CHICAGOBULLETPROOF.COM

DT DOOR/FRAME

MATERIAL: SHOT-TEX FINISH: PRIME PAINTED, FINISH PAINTED, OR STAINLESS STEEL

DWG. NO.: DT	REVISION: 0	UL LEVEL: 1-4, 6 & 8	GLAZING: TBD	TOLERANCES: +/-1/16"	SCALE: 1-1
--------------	-------------	----------------------	--------------	----------------------	------------

SHEET: 1 OF 1	WEIGHT: TBD
---------------	-------------