

Approved  YES  NO

Approved By: \_\_\_\_\_

Date: \_\_\_\_\_

# MAXROLL

-	STANDARD SYSTEM INCLUDES
-	SBR RUBBER CURTAIN - BLACK
-	BREAKAWAY BOTTOM BAR
-	RUBBER ASTRAGAL BOTTOM SEAL
-	10,000 CYCLE SPRING
-	LINTEL BRUSH SEAL
-	MANUAL CHAIN HOIST
-	HEAVY-DUTY POWDER-COATED GUIDES

-	MECHANICAL / ELECTRICAL OPTIONS
-	EPDM RUBBER - GRAY OR BLUE
-	VINYL VISION PANEL: QTY. 1
-	EXTERIOR HOOD & MOTOR COVER
-	GUIDE BRUSH SEALS
-	MAXPRO LINTEL BRUSH
-	STAINLESS STEEL BOTTOM BAR
-	THERMAL CURTAIN
-	50,000 CYCLE SPRING
-	STAINLESS STEEL GUIDES

ELECTRICAL CRITERIA:  
NONE: MANUAL OPERATION

NOTES:

PROJECT:

CLIENT:

DRIVE:

MOUNT:

(484) 840 - 8500  
5 Crozerville Road | Aston, PA 19014

RIGHT HAND

INTERIOR

DRAWN

DATE

NAME

CHECKED

07/07/2020

C.LATSIOS

07/07/2020

G.PRZYDZIAL






[Qty:01] MaxRoll  
10 ft (W) x 10 ft (H)

COPYRIGHT: The design and engineering content shown on this drawing remains the property of PERFORMAX, and may not be copied in any way without prior written approval from the company.

Drawing Number  
MAXROLL - MR6830 - 120x120

Rev.  
0



RUBBER LOOP