



**Standard Lift**  
 -most common track type  
 -available in 10", 12", 15", 20" and 32" radius track



**High Lift**  
 -door travels upward past the header  
 turns horizontally into the room  
 -use when headroom is available to horizontal tracks higher than sta




**Standard Lift Incline Track**  
 -use when headroom is not a factor and track is to follow the pitch of the roof




**High Lift Incline Track**  
 -door travels upward past the header horizontally into the room and follows the pitch of the roof  
 -use when headroom is available to horizontal tracks higher than sta

call C.H.I. for headroom requirement:




**Low Headroom**  
 -use when headroom is minimal  
 -available in 12" and 15" radius track  
 -springs can be located at the header or at the rear of the track



**Low Headroom Incline Track**  
 -use when headroom is minimal and track is to follow the pitch of the roof  
 -springs can be located at the header or at the rear of the track

call C.H.I. for headroom requirements



**Vertical Lift**  
 -door travels vertically up the wall  
 -use when amount of headroom is less than the height of the door