



CUST:	MODEL #:	QTY:	# OF SECTIONS HIGH (SEE TABLE #1)	SECTIONS TO GLAZE:	SHEET 'M-28'
JOB:	DOOR WIDTH:		# OF PANELS WIDE (SEE TABLE #2)	PANELS TO GLAZE:	DATE:
ARCH:	DOOR HEIGHT:				BID #:
CONT:					PAGE of

REV. APRIL 2008

## MODEL #'s 3717, 3718

**TABLE #1  
SECTION CHART**

DOOR HEIGHT	NUMBER OF SECTIONS
8'0"	3
8'3" - 8'0"	4
8'3" - 10'0"	5
10'3" - 12'0"	6
12'3" - 14'0"	7
14'3" - 16'0"	8
16'3" - 18'0"	9
18'3" - 20'0"	10

NOTE: DOOR HEIGHT IS AVAILABLE IN 3" INCREMENTS

**TABLE #2  
PANEL CHART**

DOOR WIDTH	NUMBER OF PANELS
7'0" - 9'2"	2
9'4" - 13'2"	3
13'4" - 16'2"	4
16'4" - 20'2"	5
20'4" - 24'2"	6
24'4" - 28'2"	7

NOTE: DOOR WIDTH IS AVAILABLE IN 2" INCREMENTS

**TABLE #3  
LITE AVAILABILITY CHART**

WINDOW SIZE	DOOR WIDTH	LITES PER SECTION
24" x 8"	7'0" - 9'2"	2
	9'4" - 13'2"	3
	13'4" - 16'2"	4
	16'4" - 20'2"	5
	20'4" - 24'2"	6
24" x 12"	24'4" - 28'2"	7
	7'0" - 9'2"	2
	9'4" - 13'2"	3
	13'4" - 16'2"	4
	16'4" - 20'2"	5
20'4" - 22'2"	6	

**TABLE #4  
REINFORCEMENT CHART**

DOOR WIDTH	DOOR HEIGHT				
	UP TO 8'0"	8'3" TO 10'0"	10'3" TO 14'0"	14'3" TO 18'0"	18'3" TO 20'0"
UP TO 12'2"	NONE	NONE	NONE	NONE	NONE
12'4" TO 14'2"	1 ea. 2-1/4"	1 ea. 2-1/4"	1 ea. 2-1/4"	1 ea. 2-1/4"	1 ea. 2-1/4"
14'4" TO 18'2"	1 - 2-1/4" per sec	1 - 2-1/4" per sec	1 - 2-1/4" per sec	1 - 2-1/4" per sec	1 - 2-1/4" per sec
18'4" TO 18'2"	1 - 3" per sec	1 - 3" per sec	1 - 3" per sec	1 - 3" per sec	1 - 3" per sec
18'4" TO 22'2"	1 - 3" per sec	1 - 4"CC per sec	1 - 4"CC per sec	1 - 4"CC per sec	1 - 4"CC per sec
22'4" TO 28'2"	1 - 4"CC per sec	1 - 4"CC per sec	1 - 4"CC per sec	1 - 4"CC per sec	1 - 4"CC per sec

