



REMARK :  
 1.HDGS:Hot Dip Galvanized Steel.  
 2.A.C: Aluminum Alloy Cast

Item	Description	M.T	Specification	Qt'y
1	Fan Motor		1 1/2HP*8P	1 pcs
2				
3	Motor Frame Ass'y	HDGS		1 set
4	Fan	A.C	LSF-120	1 set
5	Fan Guard	HDGS		1 set
6	Casing	F.R.P		4 pcs
7	Hand Hole	E.V.A		1 pcs
8	Sprinkler Head		LSH-080	1 set
9	Sprinkler Pipe	P.V.C		4 pcs
10	Eliminator	P.V.C		4 pcs
11				
12	Stand Pipe	P.V.C		1 set
13	Filling	P.V.C		1 set
14	Stopper or Column	A.C		1 set
15	Filling Supportor	HDGS		1 set
16	Casing Supportor	Nylon		4 pcs
17	Inlet Louver	P.V.C		1 set
18				
19	Water Basin	F.R.P		2 pcs
20	Water Sump	F.R.P		1 pcs
21	Ladder	HDGS		1 set
22	Strainer	P.E		1 pcs
23				
24				

Drain	25A( 1 ")	Over Flow	25A( 1 ")
Outlet	80A( 3 ")		
Inlet	80A( 3 ")	Automatic Filler	20A(3/4")
Pipe Connections			
Dry Weight	504 LBS	Operating Weight	1,472 LBS
Loading Data			
Ambient Wetbulb	75°F	Air Volume	14,700 Ft <sup>3</sup> /MIN
Outlet Water Temp	85°F	Water Flow	177 G/MIN
Inlet Water Temp	95°F	Cooling Capacity	885,000 BTU/HR

Design Condition				
Modified No.	Date	Modifier	Approver	NOTE
	T-260			C.T.S
TITLE	Cooling Tower Outling Drawing			
Approved		Designed		IN / '07 · 2 · 14
Checked		Drawn		DWG NO.

LIANG CHI INDUSTRY CO., LTD.