

DaVinci Custom Fireplace™  
STYLE: ISLAND 96" x 12"

Electrical Req'd - 7A 120V      Gas Req'd - 101,500 BTU's

NG - Min = 5.5"wc (1.37kpa), Max = 7"wc (1.74 kpa)  
LP - Min = 11"wc (2.74 kpa), Max = 13"wc (3.23 kpa)

