

DaVinci Custom Fireplace™

STYLE: SINGLE SIDED/SEE THRU 120" x 20"

Electrical Req'd - 7A 120V

Gas Req'd - 145,000 BTU's

NG - Min = 5.5"wc (1.37kpa), Max = 7"wc (1.74 kpa)

LP - Min = 11"wc (2.74 kpa), Max = 13"wc (3.23 kpa)

