



#### PARTS DESCRIPTION

- ① #12x1" H.H. TEK SCREWS  
4" FROM EACH END & 12"-14" O.C.
- ② #12x1" SDS TT25 COUNTERSINK HEAD,  
1" FROM EDGE ON VERTICALS,  
3" FROM EDGE ON HORIZONTALS,  
14"-16" O.C. THEREAFTER.  
REQUIRES 1/4" HOLE DRILLED IN .375 DEFENSE LITE.
- ③ 1" WIDE HIGH BOND TAPE  
1" TUBE TO EXISTING FRAMING.
- ④ 3/4" WIDE HIGH BOND TAPE  
1" TUBE TO NEW .375 DEFENSE LITE.
- ⑤ 3/4" WIDE HIGH BOND TAPE  
NEW 1" ANGLE TO NEW .375 DEFENSE LITE.
- ⑥ 1" x 1" x .125 (6063) ALUM. TUBE
- ⑦ 1" x 1/2" x .125 (6061) ALUM. ANGLE
- ⑧ DOW 995 PERIMETER SEALANT
- ⑨ .375 DEFENSE LITE
- ⑩ VENT CAP - P/N FV1 (BLACK), (GREY), OR (WHITE).  
6" FROM EACH END & 24" O.C.  
STAGGERED FOR SYMMETRY ON EACH SIDE.



VENT CAP INSTALLED AFTER ALL  
FRAME FASTENING AND  
VENTILATION WORK IS COMPLETED.

## TRANSOM BAR

4

D.2

ARCH. DETAIL REF.:  
ARCH. SHEET REF.:

**DEFENSELITE®**

info@impactsecurity.com | 888-689-5502 | defense-lite.com