



#### PARTS DESCRIPTION

- ① #12 x 2" S.S. WITH SECURITY TIP & CSK WASHER  
4" FROM EACH END & 12" O.C
- ② #12 x 1" S.S. WITH SECURITY TIP  
3" FROM EACH END & 12" O.C.  
REQUIRES  $\frac{1}{4}$ " HOLE DRILLED IN .236 DEFENSE LITE.
- ③ 1" WIDE HIGH BOND TAPE  
1" TUBE TO EXISITING FRAMING.
- ④  $\frac{3}{4}$ " WIDE HIGH BOND TAPE  
1" TUBE TO NEW .236 DEFENSE LITE.
- ⑤  $\frac{3}{4}$ " WIDE HIGH BOND TAPE  
NEW 1" FLAT BAR TO NEW .236 DEFENSE LITE.
- ⑥ 1" x 1" x .125 (6063) ALUM. TUBE
- ⑦ 1" x .125 (6061) FLAT ALUM. BAR
- ⑧ DOW 795 PERIMETER SEALANT
- ⑨ .236 DEFENSE LITE
- ⑩ .375 DEFENSE LITE
- ⑪ VENT CAP – P/N FV1 (BLACK), (GREY), OR (WHITE).  
6" FROM EACH END & 24" O.C.  
STAGGERED FOR SYMMETRY ON EACH SIDE.

8 TRANSOM  
D.2 ARCH. DETAIL REF.:  
ARCH. SHEET REF.:

**DEFENSELITE®**

info@impactsecurity.com | 888-689-5502 | defenselite.com