


HIP AND RIDGE

MC-18A



Note:

Openings at hips, ridges and head walls including chimneys, skylights, solar panels, and downslope horizontal abutments shall be fitted with weather blocking material to keep water on the surface of the field tile. Other methods approved by local building official will be allowed. See Technical Bulletin at www.Tilerroofing.org

Wrapping of nailer board is optional except with the use of mortar. (All profiles of tile)

Notes:

1. One layer of No. 30 asphalt-saturated felt complying with ASTM D-226 Type II (ASTM D4869 Type IV) as a minimum underlayment on all tile roof applications. Other underlayments as approved by local building officials will be allowed.
2. All hip and ridge tile are required to have a code approved adhesive or special clip between laps of trim tile.
3. For tile fastening schedule(s) see Fastening Table 1A and 1B.
4. Battens for tiles with protruding anchor lugs are optional for slopes between 3:12 and 7:12. Direct deck attachment of tile as approved by local building official will be allowed.
5. Roofer's mastic or tile adhesive must be applied at hip and ridge trim headlap to cover nail hole and create a bond between ridge tiles.