



Letter	Inches	Millimeters
A	5 ¹⁵ / ₁₆	150
B	34 ¹ / ₄	869
C	42 ¹ / ₁₆	1084
D	2 ¹³ / ₁₆	71
E	32 ¹ / ₁₆	814
F	⁵ / ₈	15
G	11 ⁵ / ₈	319
H	37 ¹³ / ₁₆	961
I	35	889
J	26 ¹ / ₂	672
K	3 ³ / ₁₆	96
L	8 ⁷ / ₈	224
M	12 ⁹ / ₁₆	319
N	6 ⁵ / ₁₆	160

For proper operation, all Element4 fireplaces require a warm air outlet to be set in the enclosing wall. Please see the installation Manual for further details.



Framing Dimensions (Noncombustible Framing)	
Xt	46 ³ / ₄ " / 1184mm
Yt	12 ⁹ / ₁₆ " / 319mm
Z	39" / 986mm

This information is for reference only. Please consult the Installation Manual for all details prior to making any design decisions.
Conversions from millimeters are rounded to the nearest fraction.