



DRL - Flat Roof Access Hatch

A	B	Y	S	L'	H'
27 ⁷ / ₁₆ "	51 ¹ / ₁₆ "	59 ¹ / ₂ "	35 ³ / ₈ "	68 ¹⁵ / ₁₆ "	66 ¹⁵ / ₁₆ "

748 - FAKRO DRL 70x130 cm (AxB) - US model 27.5"x59.5" (AxY)
 Flat roof hatch
 764 - FAKRO LML Metal attic ladder

K	E	G	S
Folded ladder height	Tread length	Distance between treads	Tread width
12 ¹ / ₂ "	13 ³ / ₄ "	9 ³ / ₁₆ "	5 ¹ / ₈ "

Lader Model #	LML - Loft ladder dimensions									
	H	A	B	R	C	WxL	MxN	J	D	Z
	Ceiling height	Rough opening	Rough opening	Projection	Landing space	Outside frame dimension	Internal frame dimensions	Loft ladder width with trims	Loft ladder length with trims	Roof Step depth
862411	7'7 ³ / ₄ " - 9'2 ¹ / ₄ "	27 ¹ / ₂ "	47"	65"	47 ¹ / ₄ "	27"x46 ³ / ₄ "	25 ¹ / ₄ "x44 ⁷ / ₈ "	28 ¹ / ₂ "	48 ¹ / ₄ "	13 ³ / ₈ "
862453	9'2 ³ / ₄ " - 10'3"	27 ¹ / ₂ "	51"	69 ¹ / ₂ "	51 ¹ / ₄ "	27"x50 ⁷ / ₈ "	25 ¹ / ₄ "x48 ⁷ / ₈ "	28 ¹ / ₂ "	52 ¹ / ₄ "	9 ¹ / ₂ "

FAKRO



Technical drawing:
 LML 3-section loft ladder with metal ladder, DRL
 FAKRO Flat Roof Access Hatch

FORMAT:
 Letter

SCALE:
 1:20

DATE:
 12.2018

Warning! The present drawing is for informational-demonstrative purposes only and as such cannot constitute a basis for performance. All dimensions presented in this drawing should be verified on site. Because of the fact that the drawing is a schematic one, FAKRO shall not assume any responsibility for the actual installation quality. This drawing is FAKRO's property and cannot be published or used publicly without our written consent.