



- 1-Water draining gutter FAKRO
- 4-XDP FAKRO vapour permeable collar
- 5-Tress made of sheep wool FAKRO (XDP)
- 6-Blocks made of sheep wool FAKRO (XDP)
- 8-XLW internal lining element FAKRO
- 17-Rafter
- 38-Installation bracket
- 109-XDS air-tight flashing FAKRO
- 158-ELV flashing side element FAKRO
- 159-ELV flashing upper element FAKRO
- 160-ELV flashing lower element FAKRO
- 233-FPP-V L3, FPU-V L3 preSelect top hung and pivot window FAKRO

FPP-V L3, FPU-V L3 preSelect		
Frame width S[mm]	Frame height H[mm]	Window symbol
547	980	02
	1180	16
657	980	03
	1180	04
777	980	05
	1180	06
	1400	07
	1600	13
937	980	15
	1180	08
	1400	09
	1600	80*
1137	980	20
	1180	10
	1400	11
1337	980	12
	1180	18**
	1400	17*

*- with roller shutter ARZ - 35°-55°
 **-only without roller shutter ARZ

FAKRO		FORMAT: A4	SCALE: 1:10/1:5	DATE: 06.2012
FPP-V L3 preSelect FPU-V L3 preSelect	ELV	SLATE	XLW	15° - 55°

Warning! The present drawing is for informational-demonstrative purposes only and as such cannot constitute a basis for performance. All dimensions presented in this drawing should be verified on site. Because of the fact that the drawing is a schematic one, FAKRO shall not assume any responsibility for the actual installation quality on the roof. This drawing is FAKRO's property and cannot be published or used publicly without our written consent.

Vertical and horizontal cross-section:
 FPP-V L3 preSelect, FPU-V L3 preSelect top hung
 and pivot window with ELV flashing for flat tiled roofs