



- 1-Water draining gutter FAKRO
- 4-XDP FAKRO vapour permeable collar
- 5-Tress made of sheep wool FAKRO (XDP)
- 6-Blocks made of sheep wool FAKRO (XDP)
- 8-XLW internal lining element FAKRO
- 17-Rafter
- 38-Installation bracket
- 109-XDS air-tight flashing FAKRO
- 158-ELV flashing side element FAKRO
- 159-ELV flashing upper element FAKRO
- 160-ELV flashing lower element FAKRO
- 377-FTP-V5 U3, FTU-V5 U3 pivot window FAKRO

FTP-V5 U3, FTU-V5 U3		
Frame width S[mm]	Frame height H[mm]	Window symbol
457	780	46
	980	48
477	780	47
	980	49
547	780	01
	980	02
	1180	16
	780	22
657	980	03
	1180	04
	1400	14
	780	23
	980	05
777	1180	06
	1400	07
	1600	13
	780	24
	980	15
937	1180	08
	1400	09
	1600	80
	780	25
	980	20
1137	1180	10
	1400	11
	1600	50
	780	26
	980	12
1337	1180	18
	1400	17

	FTP-V5 U3 FTU-V5 U3	ELV	SLATE	XLW	15° - 90°
Vertical and horizontal cross-section: FTP-V5 U3, FTU-V5 U3 roof window with ELV flashing for flat tiled roofs			FORMAT: A4	SCALE: 1:10/1:5	DATE: 12.2011

Warning! The present drawing is for informational-demonstrative purposes only and as such cannot constitute a basis for performance. All dimensions presented in this drawing should be verified on site. Because of the fact that the drawing is a schematic one, FAKRO shall not assume any responsibility for the actual installation quality on the roof. This drawing is FAKRO's property and cannot be published or used publicly without our written consent.