



FTT U6		
Frame width S[mm]	Frame height H[mm]	Window symbol
547	981	02
	1181	16
657	981	03
	1181	04
	1401	14
777	981	05
	1181	06
	1401	07
	1601	13
937	981	15
	1181	08
	1401	09
	1601	80
	981	20
1137	1181	10
	1401	11
	1601	50
1337	981	12
	1181	18
	1401	17

Warning! The present drawing is for informational-demonstrative purposes only and as such cannot constitute a basis for performance. All dimensions presented in this drawing should be verified on site. Because of the fact that the drawing is a schematic one, FAKRO shall not assume any responsibility for the actual installation quality on the roof. This drawing is FAKRO's property and cannot be published or used publicly without our written consent.

	Vertical and horizontal cross-section: FTT U6 roof window with ELV-AT THERMO flashing for flat tiled roofs		FORMAT: A4	SCALE: 1:10/1:5	DATE: 04.2012