


- 78-Spring
- 80-Tread
- 84-Thermo-insulated hatch
- 85-Ladder bracket
- 86-Hinge
- 88-Side bracket
- 90-handrail
- 93-stile end
- 94-Stringer (ladder side element)

E	G	S
Tread length	Distance between treads	Tread width
[cm]	[cm]	[cm]
35	25	13

Loft ladder dimensions									
H	A	B	K	R	C	T	WxL	MxN	JxD
Room height	Width ceiling opening dimensions	Length ceiling opening dimensions	Folded ladder height	Swing space	Distance after ladder unfolding	Box height	Box external dimensions	Internal box dimensions	Loft ladder dimensions with trims
[cm]	[cm]	[cm]	[cm]	[cm]	[cm]	[cm]	[cm]	[cm]	[cm]
280	60	120	31,5	165	120	31,5	59,6x118,6	55x114	63,6x122,6
	70	120					68,6x118,6	64x114	72,6x122,6
	70	130					68,6x128,6	64x124	72,6x132,6
	70	140					68,6x138,6	64x134	72,6x142,6
	86	130					84,6x128,6	80x124	88,6x132,6
305	92	130	176	130	130	31,5	90,6x128,6	88x124	94,6x132,6
	60	130					59,6x128,6	55x124	63,6x132,6
	70	130					68,6x128,6	64x124	72,6x132,6
	70	140					68,6x138,6	64x134	72,6x142,6
	86	130					84,6x128,6	80x124	88,6x132,6
	92	130					90,6x128,6	88x124	94,6x132,6

FAKRO

LML



Warning! The present drawing is for informational-demonstrative purposes only and as such cannot constitute a basis for performance. All dimensions presented in this drawing should be verified on site. Because of the fact that the drawing is a schematic one, FAKRO shall not assume any responsibility for the actual installation quality. This drawing is FAKRO's property and cannot be published or used publicly without our written consent.

Technical drawing:
LML 3-section loft ladder with metal ladder

FORMAT:
A4

SCALE:
1:20/1:10

DATE:
04.2017