



ITEM: INTERNAL THREAD ADJUSTER

MATERIAL: TYPE 316 STAINLESS STEEL

FITTING TYPE: ADJUSTABLE CABLE END FITTING FOR ATTACHING & TENSIONING LINES.

SWAGE TYPE: MACHINE HEX SWAGE AT FACTORY (NOT AVAILABLE IN CABLECRIMP STYLE)

POST TYPE: METAL OR WOOD POSTS (POSTS NOT INCLUDED)

FASTENING TO POST: ATTACH THROUGH HOLE IN END/TERMINATION POST USING BOLT & FLAT WASHER (INCLUDED)

FASTENING AT ANGLES: DRILL POST HOLES AT ANGLES AND USE BEVELED WASHERS.

CABLE TENSIONING: ADJUST BY TIGHTENING BOLT.

HARDWARE PAIRINGS: USUALLY PAIRED WITH ANOTHER INTERNAL THREAD ADJUSTER. MAY ALSO USE ANY FIXED END OR TENSION ADJUSTMENT FITTING.

SUPPLIER: FEENEY, INC.

INTERNAL THREAD ADJUSTER, STAINLESS STEEL

| PART# | SWAGE TYPE | CABLE SIZE | THREAD SIZE | WASHER DIA. (WØ) | HEAD & WASHER THICKNESS (CT) | BODY LENGTH (BL) | LENGTH CLOSED (OPEN) (L) | BEFORE SWAGE DIAM. (SBØ) | ATTACHMENT POST DRILL HOLE Ø |
|----------|------------|------------|-------------|------------------|------------------------------|------------------|--------------------------|--------------------------|------------------------------|
| 3266-1.5 | MACHINE | 1/8" | 10-24 RH | 7/16" | 1/8" | 2-1/2" | 2-3/4" (3-3/4") | 1/4" | 5/16" |
| 3266-2 | MACHINE | 1/8" | 10-24 RH | 7/16" | 1/8" | 2-1/2" | 3-1/4" (4-1/4") | 1/4" | 5/16" |
| 3266-3 | MACHINE | 1/8" | 10-24 RH | 7/16" | 1/8" | 2-1/2" | 4-1/4" (5-1/4") | 1/4" | 5/16" |
| 3267-1.5 | MACHINE | 3/16" | 1/4-20 RH | 11/16" | 3/16" | 3" | 3-1/4" (4-1/4") | 11/32" | 3/8" |
| 3267-2 | MACHINE | 3/16" | 1/4-20 RH | 11/16" | 3/16" | 3" | 3-3/4" (4-3/4") | 11/32" | 3/8" |
| 3267-3 | MACHINE | 3/16" | 1/4-20 RH | 11/16" | 3/16" | 3" | 4-3/4" (5-3/4") | 11/32" | 3/8" |

CableRail Reference Drawing:
INTERNAL THREAD ADJUSTER

THIS DRAWING IS THE PROPERTY OF FEENEY INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF FEENEY INC. IS STRICTLY PROHIBITED.

DATE: 05/15/13
PAGE: 1 of 1
REV: A (12/15/17) MRJ
BY: DSY
CHK: BWA

feeney 
2603 Union St., Oakland, CA 94607
P: 800-888-2418 F: 510-893-9484
www.feeneyinc.com