



ITEM: QUICK-CONNECT<sup>®</sup> INSET  
 MATERIAL: STAINLESS STEEL BODY AND INTERNAL JAWS  
 FITTING TYPE: SEMI-ADJUSTABLE, SELF-LOCKING CABLE END FITTING  
 SWAGE TYPE: SELF-LOCKING JAWS (NO SWAGING)  
 POST TYPE: METAL OR WOOD (POSTS NOT INCLUDED).  
 FASTENING TO POST: PASS CABLE THROUGH HOLE IN END/TERMINATION POST, SLIDE FITTING ONTO CABLE AND PULL TIGHT. FITTING AUTOMATICALLY GRABS AND LOCKS.  
 FASTENING AT ANGLES: DRILL HOLES AT ANGLE AND USE BEVELED WASHERS.  
 CABLE TENSIONING: ADJUSTABLE BY PULLING CABLE THROUGH FITTING. (NOT DESIGNED AS FINAL TENSIONING FITTING)  
 HARDWARE PAIRINGS: USUALLY PAIRED WITH A THREADED TERMINAL FITTING. MUST BE USED WITH A TENSION ADJUSTMENT<sup>®</sup> FITTING; DO NOT USE WITH ANOTHER QUICK-CONNECT<sup>®</sup> INSET FITTING.  
 SUPPLIER: FEENEY, INC.

QUICK-CONNECT<sup>®</sup> INSET FITTING. STAINLESS STEEL

PART#	SWAGE TYPE	CABLE SIZE	BODY DIA (BØ)	END DIA (CØ)	END THICK (CT)	LENGTH (L)	ATTACHMENT POST DRILL HOLE Ø
3146	SELF-LOCKING	1/8"	3/8"	5/8"	1/8"	1-1/8"	3/8"
3147	SELF-LOCKING	3/16"	17/32"	3/4"	1/4"	1-5/8"	9/16"
3148	SELF-LOCKING	1/4"	17/32"	3/4"	1/4"	1-5/8"	9/16"

CableRail Reference Drawing:  
**QUICK-CONNECT<sup>®</sup>**

THIS DRAWING IS THE PROPERTY OF FEENEY INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF FEENEY INC. IS STRICTLY PROHIBITED.

DATE:	05/15/13
PAGE:	1 of 1
REV:	A (12/07/17) MRJ
BY:	DSY
CHK:	BWA

**feeney**   
 2603 Union St., Oakland, CA 94607  
 P: 800-888-2418 F: 510-893-9484  
 www.feeneyinc.com