


2.67⁹⁹ x 3/4⁹⁹

Corrugated Standard Details



3/4" Corrugated Load Table

Span Length

Thickness	# Spans	4'	4' 6"	5'	5' 6"	6'	6' 6"	7'	7' 6"	8'	8' 6"	9'	9' 6"	10'
18 Ga STL.	1	107	85	69	57	48	41	35	31	27	24	21	-	-
	3	134	106	86	71	60	51	44	38	34	30	27	24	22
20 Ga STL.	1	82	64	52	43	36	31	27	23	20	-	-	-	-
	3	102	81	65	54	45	39	33	29	26	23	20	-	-
22 Ga STL.	1	92	73	59	49	41	35	30	26	23	20	-	-	-
	3	115	91	74	61	51	44	38	33	29	26	23	20	-
24 Ga STL.	1	74	59	48	39	33	28	24	21	-	-	-	-	-
	3	93	73	59	49	41	35	30	26	23	21	-	-	-
26 Ga STL.	1	56	44	36	30	25	21	-	-	-	-	-	-	-
	3	70	55	45	37	31	27	23	20	-	-	-	-	-

Stress governing, 37 ksi yield for 18, 20 Ga; 50 ksi for 22, 24 and 26 Ga

FLEXOSPAN RESERVES THE RIGHT TO REVISE, ADD, OR DELETE ANY DETAIL OR INFORMATION HEREIN WITHOUT PRIOR NOTICE.



BOX 515 RAILROAD STREET
SANDY LAKE, PENNSYLVANIA 16145-0515
PHONE: 800-245-0396 ° FAX: 724-376-3864

2.67" x 3/4" Corrugated
Standard Details

DRAWN BY: D. UREY

DATE: 9/20/05

DRAWING NO.

CHECKED BY:

DATE:

COVER

2.67" x 3/4" - C