


2.67" x 7/8"

Corrugated Standard Details



7/8" Corrugated Load Table

Span Length

Thickness	# Spans	4'	4' 6"	5'	5' 6"	6'	6' 6"	7'	7' 6"	8'	8' 6"	9'	9' 6"	10'
18 Ga STL.	1	136	107	87	72	60	51	44	38	34	30	26	24	21
	3	170	134	108	90	75	64	55	48	42	37	33	30	27
20 Ga STL.	1	103	81	66	54	45	39	33	29	25	22	20	18	16
	3	129	101	82	68	57	48	42	36	32	28	25	22	20
22 Ga STL.	1	116	92	74	61	51	44	38	33	29	25	23	20	18
	3	145	115	93	77	64	55	47	41	36	32	28	25	23
24 Ga STL.	1	93	74	60	49	41	35	30	26	23	20	18	16	15
	3	117	92	75	62	52	44	38	33	29	25	23	20	18
26 Ga STL.	1	70	55	45	37	31	26	23	20	17	15	13	12	-
	3	88	69	56	46	39	33	28	25	22	19	17	15	14
0.040 Aluminum	1	65	51	41	34	28	24	21	18	16	14	12	-	-
	3	81	64	52	43	36	30	26	23	20	18	16	14	13
0.032 Aluminum	1	52	41	33	27	23	19	17	14	13	-	-	-	-
	3	65	51	41	34	29	24	21	18	16	14	12	-	-

Stress governing, 37 ksi yield for 18, 20 Ga; 50 ksi for 22, 24 and 26 Ga

FLEXOSPAN RESERVES THE RIGHT TO REVISE, ADD, OR DELETE ANY DETAIL OR INFORMATION HEREIN WITHOUT PRIOR NOTICE.



BOX 515 RAILROAD STREET
SANDY LAKE, PENNSYLVANIA 16145-0515
PHONE: 800-245-0396 ° FAX: 724-376-3864

2.67" x 7/8" Corrugated
Standard Details

DRAWN BY: D.UREY

DATE: 9/20/05

DRAWING NO.

CHECKED BY:

DATE:

COVER

2.67" x 7/8" - C