

"FSS-1.5" STANDARD TRIM SKETCHES

GA. # _____ COLOR _____

REQ'D: _____ PCS. @ 10'-0" LG.

GA. # _____ COLOR _____

41 7/8

REQ'D: _____ PCS. @ 10'-0" LG.

"FSS15-08" BASE ROOF FLASH

GA. # _____ COLOR _____

44"

(18 GA. MIN.)

REQ'D: _____ PCS. @ 10'-0" LG.

"FSS15-04" VALLEY FLASHING

GA. # _____ COLOR _____

20"

REQ'D: _____ PCS. @ 10'-0" LG.

"FSS15-05" VALLEY PLATE

"GT3" HI EAVE TRIM

NOTES:

1. ALL TRIM IS MANUFACTURED IN 10'-0" LENGTHS UNLESS SPECIFIED OTHERWISE.
2. MAXIMUM LENGTH OF TRIM IS 10'-0".
3. PLEASE INSERT GAUGE OF MATERIAL IN SPACES PROVIDED.
4. PLEASE INSERT COLOR OF MATERIAL IN SPACES PROVIDED.
5. PLEASE INSERT QUANTITY DESIRED WHERE SHOWN.
6. PLEASE INSERT REQ'D DIMENSIONS.



BOX 515 RAILROAD STREET
SANDY LAKE, PENNSYLVANIA 16145-0515
PHONE: 800-245-0396 • FAX: 724-376-3864

"FSS-1.5" Standing
Seam Details

"Fss-1.5" Standard Trim
Sketches

DRAWN BY: D.UREY

DATE: 9-27-05

DRAWING NO.

REVISED BY:

DATE:

FSS15-22