


# "Fss-316" Standing Seam Roof System



ALLOWABLE UNIFORM LOAD (DEAD + LIVE) LBS. PER SQ. FT.														
DEFLECTION LOADS ARE CALCULATED FOR A LIVE LOAD DEFLECTION NOT IN EXCESS OF L/180 OF THE SPAN														
SPAN CONDITION	ASTM A446 GRADE	SPAN LENGTH (FT.)												
		GAGE	5.0	5.5	6.0	6.5	7.0	7.5	8.0	8.5	9.0	9.5	10.0	10.5
SIMPLE SPAN	D	24	90	81	68	57	49	42	37	32	28	25	22	20
		22	146	120	100	85	73	63	55	48	42	38	34	30
TWO SPAN	D	24	87	74	63	53	46	40	35	31	28	25	22	20
		22	125	104	87	74	64	56	49	43	38	34	31	28
THREE SPAN	D	24	87	79	73	66	57	50	44	39	34	31	28	25
		22	144	129	108	92	80	69	61	54	48	43	39	35

FLEXOSPAN RESERVES THE RIGHT TO REVISE, ADD, OR DELETE ANY DETAIL OR INFORMATION HEREIN WITHOUT PRIOR NOTICE.

**FLEXOSPAN**  
 BOX 515 RAILROAD STREET  
 SANDY LAKE, PENNSYLVANIA 16145-0515  
 PHONE: 800-245-0396 ° FAX: 724-376-3864

"Fss-316" Standing Seam  
 Details

DRAWN BY: RW  
 CHECKED BY: CANON  
 DATE: 8/31/00  
 DATE:

Cover  
 DRAWING NO.  
 FSS316-C