


2.67⁹⁹ x 1/2⁹⁹

Corrugated Standard Details



1/2" Corrugated Load Table

Span Length

Thickness	# Spans	2' 6"	3'	3' 6"	4'	4' 6"	5'	5' 6"	6'	6' 6"	7'	7' 6"	8'
18 Ga STL.	1	150	104	76	58	46	37	31	26	22	19	16	14
	3	187	130	95	73	57	46	38	32	27	23	20	18
20 Ga STL.	1	114	79	58	44	35	28	23	19	17	14	12	-
	3	143	99	73	56	44	35	29	24	21	18	16	14
22 Ga STL.	1	130	90	66	51	40	32	27	22	19	16	14	12
	3	163	113	83	63	50	40	33	28	24	20	18	15
24 Ga STL.	1	105	73	53	41	32	26	21	18	15	13	-	-
	3	131	91	67	51	40	32	27	22	19	16	14	12
26 Ga STL.	1	79	55	40	31	24	19	16	13	-	-	-	-
	3	99	69	50	38	30	24	20	17	14	12	-	-

Stress governing, 37 ksi yield for 18, 20 Ga; 50 ksi for 22, 24 and 26 Ga

FLEXOSPAN RESERVES THE RIGHT TO REVISE, ADD, OR DELETE ANY DETAIL OR INFORMATION HEREIN WITHOUT PRIOR NOTICE.



BOX 515 RAILROAD STREET
SANDY LAKE, PENNSYLVANIA 16145-0515
PHONE: 800-245-0396 ° FAX: 724-376-3864

2.67" x 1/2" Corrugated
Standard Details

DRAWN BY: D. UREY

DATE: 9/20/05

DRAWING NO.

CHECKED BY:

DATE:

COVER

2.67" x 1/2" - C