



NOTES:

1. ALLOW 2" [52 mm] CLEARANCE AROUND THE PROJECTION; IF MULTIPLE PROJECTIONS EXIST, ALLOW 1" [25.4 mm] BETWEEN THE PROJECTION & POCKET.
2. THE EXISTING PROJECTION(S) MUST BE CLEAN OF ALL DEBRIS PRIOR TO INSTALLATION.
3. FOUR DRILL-TEC™ PLATES & SCREWS MUST BE FASTENED AROUND PENETRATION.
4. EVERGUARD® POURABLE SEALANT POCKET MUST BE PRIMED WITH TPO PRIMER OR LOW VOC TPO PRIMER.
5. IF THE SEALANT POCKET MUST BE CUT, STRIP IN CUT WITH UNREINFORCED TPO STRIP 4" [102 mm] WIDE MINIMUM AND RUN OUT ONTO DECK SHEET 2" [52 mm] MINIMUM.
6. IF PLATES AND FASTENERS ENCROACH INTO THE SEAM AREA OF THE POCKET, THEN A TARGET PATCH MUST BE ADDED FIRST TO THE COVER FASTENERS.
7. POURABLE SEALANT IS CONSIDERED A MAINTENANCE ITEM AND IS EXCLUDED FROM GUARANTEE COVERAGE.

LEGEND		POURABLE SEALANT POCKET			DETAIL
	HEAT WELD				525
	SEALANT				
		ROOF AREA	ISSUE DATE	SCALE	
		PENETRATIONS	07/26/22	6" = 1'	