


SINGLE-PLY: TPO & PVC

ALTERNATE INSTALLATION



SEE NOTE #2

EVERGUARD® PREMOLDED VENT BOOT
TARGET MADE FROM REINFORCED
EVERGUARD® MEMBRANE

STAINLESS
STEEL CLAMP

DRILL-TEC™ PLATES
& FASTENERS
4 PER PENETRATION

ROOF
DECK/SUBSTRATE

VENT STACK

EVERGUARD® WATER BLOCK OR
FLEXSEAL™ CAULK GRADE SEALANT

EVERGUARD® PREMOLDED VENT BOOT

REINFORCED
EVERGUARD®
MEMBRANE

MULTIPLE LAYERS OF
ENERGYGUARD™
ROOF INSULATION

NOTE:

1. DO NOT CUT SIDE OF PREMOLDED BOOT. IT MUST BE PULLED OVER VENT PIPE.
2. IF THE PLATES AND FASTENERS INTRUDE INTO BOOT FLANGE AREA, THEN A TARGET MUST FIRST BE INSTALLED OVER PLATES AND FASTENERS BEFORE BOOT INSTALLATION.
3. FOR INSULATION THICKNESS GREATER THAN 8" (203 mm), A COVER BOARD IS REQUIRED ON MECHANICALLY ATTACHED SYSTEMS ONLY.
4. 25 YEAR GUARANTEES AND ABOVE MUST USE EXTREME ACCESSORIES.

GAF

PREMOLDED VENT BOOT FLASHING DETAIL

DRAWING #

506A

THIS DETAIL APPLIES TO:

ALL SYSTEMS

ISSUE / REVISION DATE

8/17/20

SCALE

N.T.S.

LEGEND

HEAT-WELDED

FLEXSEAL™ CAULK GRADE SEALANT