



NOTE:

1. ALLOW 2" (52 mm) CLEARANCE AROUND THE PROJECTION. IF MULTIPLE PROJECTIONS, ALLOW 1" (25.4 mm) BETWEEN PROJECTION AND POCKET.
2. THE EXISTING PROJECTION MUST BE CLEAN OF ALL DEBRIS BEFORE INSTALLATION.
3. FOUR DRILL-TEC™ PLATES & SCREWS INSERTED AROUND PENETRATION.
4. EVERGUARD® POURABLE SEALER POCKET MUST BE PRIMED WITH EVERGUARD® TPO PRIMER (TPO ONLY).
5. IF SEALANT POCKET MUST BE CUT, STRIP IN CUT WITH UNREINFORCED TPO OR PVC STRIP MIN 4" (102 mm) WIDE AND RUN OUT ONTO DECK SHEET MINIMUM 2" (52 mm).
6. 25 YEAR GUARANTEES AND ABOVE MUST USE EXTREME ACCESSORIES (TPO ONLY).
7. IF PLATES AND FASTENERS ENCROACH INTO THE SEAM AREA OF THE POCKET, THEN A TARGET MUST BE ADDED FIRST TO COVER FASTENERS.
8. POURABLE SEALANT IS CONSIDERED A MAINTENANCE ITEM AND IS EXCLUDED FROM GUARANTEE COVERAGE.

GAF

POURABLE SEALANT POCKET DETAIL

DRAWING #
525

THIS DETAIL APPLIES TO:
ALL SYSTEMS

ISSUE / REVISION DATE
8/17/20

SCALE
N.T.S.

LEGEND