



FRONT VIEW II SCALE 1 : 5




SECTION A-A II SCALE 1 : 5



2" aluminum 10-24 studs standard  
(stainless steel optional)

DETAIL DW II SCALE 1 : 1

Inside radius (0.015" - 0.135"  
based on part size)



ISOMETRIC BACK VIEW II SCALE 1 : 3

NOTES:

- Designed for interior use
- Stud blocks aligned 2 5/8" on center, in horizontal rows, to align with brick mortar joints
- Stud length 2" beyond back of letter
- Optional flush stud with min. 3/8" thick acrylic
- Aluminum 10/24 studs- standard, 6/32 studs used on thin strokes
- Min. 0.30" stroke
- Standard Gemini letter styles or per vector art



TITLE: LASER CUT ACRYLIC - STUD FOR BRICK MOUNT			
MATERIAL: ACRYLIC		PRODUCT TYPE: PLASTIC LETTERS	
DWG NO. LASR80	REV. 1/29/2018	SCALE: AS INDICATED	SHEET 1 OF 1