



Scope - All high pressure plastic laminate toilet partitions shall have 1/16" general purpose laminate face and edges bonded under pressure to a solid 45lb density particle board core assuring a rigid permanent bond.

Doors & Panels - Will be 1" thick

30 Series Pilasters - Will be 1 1/4" thick. Pilasters are to be anchored to the floor with standard 3/8" threaded rod, hex nuts and washers to provide vertical adjustment and necessary strength.

Hardware - To be heavy casting non-ferrous alloy, chrome-plated. Toilet compartment will be provided with all hardware and fasteners for a complete installation for a standard installation with masonry block walls and concrete floors.

Brackets - Chrome plated stirrup brackets. Single ear will be used at pilaster to wall and end panel to walls. Double ear brackets will be used at intermediate panel to walls. U brackets will be use for panels to back of pilasters.

Door Hardware - Cutout inset type hinges work on opposing nylon cams. Top pivot pin, mounted within door having bearing points above and below hinge brackets. To be secured to pilaster with thru-bolts. ADA doors will be provided with paddle type concealed latch (with emergency access requiring no twisting motion), ADA coat hook, double sided door pull, and door bumper. Standard doors will be provided with surface mounted slide latch and combination coat hook / bumper.

Shoes - To be 3" high, .031 stainless steel.

Natural Almond D30-60	Fashion Grey D381-60	Frosty White 1573-60
Grey Glace 4142-60	Graphite Nebula 4623-60	Haze D97-60
Midway 4936-38	Eggplant 4913-60	Natural Tigris 4669-60
Green Tigris 4667-60	Brittany Blue D321-60	Aqua Fizz 4934-38
	Pewter Mesh 4878-38	Burnished Chestnut 4796-60
Pomegranate 4914-60	Navy Legacy 4651-60	Windswept Bronze 4794-60
Carbon EV 4820-60		Cream Fizz 4933-38
Pearl Soapstone 4886-38	Oiled Soapstone 4882-38	Antique Brush 4823-60
Wild Cherry 7054-60	Brazilwood 7946-38	River Cherry 7937-38
Beigewood 7850-60	Black 1595-60	Pewter Brush 4779-60

Hinge Options

- Chrome Plated Cutout Inset (Standard)
- Stainless Steel Cutout Inset
- Stainless Steel Surface Mounted (1500GS)
- Continuous Aluminum Spring Hinge (GXA2000)
- Continuous Stainless Steel Spring Hinge (JN2000)
- Continuous Stainless Steel Gravity Hinge (JN7789)

Door Hardware Options

- Chrome Plated Concealed Latch w/ Keeper
- Chrome Plated Concealed Latch w / SS Keeper
- Chrome Plated Surface Mounted Latch & Keeper
- Stainless Steel Surface Mounted Latch & Keeper

Bracket Options

- Chrome Plated Stirrup Brackets (Standard)
- Stainless Steel Stirrup Brackets
- Continuous Aluminum Brackets
- Continuous Stainless Steel Brackets

Other Options

- Aluminum Privacy Strips
- Steel Core Pilasters
- Cutouts