



Scope - Stainless Steel toilet partitions are constructed of two sheets of satin stainless steel bonded together before attaching die drawn molding on all four sides of panels. Mitered reinforcements fused to corners for added structural strength. Fillers shall be General's Ribcore sound-deadening insulation.

Doors & Panels - Will be 1" thick

50 Series Pilasters - Will be 1 1/4" thick. Pilasters are to be anchored to the overhead member (which member is to be supplied by others) with standard 3/8" threaded rod, hex nut, and washer to provide vertical adjustment and necessary strength.

Hardware - To be heavy casting non-ferrous alloy, chrome-plated. Toilet compartment will be provided with all hardware and fasteners for a complete installation for a standard installation with masonry block walls and concrete floors.

Brackets - Chrome plated stirrup brackets. Single ear will be used at pilaster to wall and end panel to walls. Double ear brackets will be used at intermediate panel to walls. U brackets will be use for panels to back of pilasters.

Door Hardware - Cutout inset type hinges work on opposing nylon cams. Top pivot pin, mounted within door having bearing points above and below hinge brackets. To be secured to pilaster with thru-bolts. ADA doors will be provided with paddle type concealed latch (with emergency access requiring no twisting motion), ADA coat hook, double sided door pull, and door bumper. Standard doors will be provided with concealed latch and combination coat hook / bumper.

Shoes - To be 3" high, .031 stainless steel.

Standard Brushed Stainless Steel	Diamond Textured Stainless Steel	Leather Grain Stainless Steel
----------------------------------	----------------------------------	-------------------------------

**Hinge Options**

- Chrome Plated Cutout Inset (Standard)
- Stainless Steel Cutout Inset
- Continuous Aluminum Spring Hinge (GXA2000)
- Continuous Stainless Steel Spring Hinge (JN2000)
- Continuous Stainless Steel Gravity Hinge (JN7789)

**Door Hardware Options**

- Chrome Plated Concealed Latch w/ Keeper (Standard)
- Chrome Plated Concealed Latch w / SS Keeper
- Chrome Surface Slide Latch & Keeper \*\*
- Stainless Steel Surface Slide Latch & Keeper \*\*

(\*\* Note: Slide Latches can ONLY be used with Continuous Hinges to allow Emergency Access)

**Bracket Options**

- Chrome Plated Stirrup Brackets (Standard)
- Stainless Steel Stirrup Brackets
- Continuous Aluminum Brackets
- Continuous Stainless Steel Brackets

**Other Options**

- Aluminum Privacy Strips
- Cutouts