

NOTE: JUNCTION BOX MAY BE PLACED ON EITHER SIDE OF EITHER DRIVE BAY DEPENDING ON PROXIMITY TO EPU.

PROPRIETARY AND CONFIDENTIAL
 THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING, ASSUMES CUSTODY THEREOF AND UNDER THE ABOVE TERMS AGREES NOT TO ALLOW USE BY UNAUTHORIZED PERSONS.
 ©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)

PATH: C:\Users\adodson\Documents\3610 drainage\



CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED		SECURE USA A Safer Future™		SecureUSA, Inc. 1649 NW 136th Ave. Sunrise, FL 33323 Toll Free: 888.222.4559 www.SecureUSA.net	
TOLERANCES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: INCHES X/X ±1/16 X ±0.1 XX ±0.02 XXX ±0.005 ANGLE ±30MIN BREAK ALL SHARP EDGES DO NOT SCALE DRAWING		DRAWN BY: AD	DESCRIPTION: 36" 12' K12 FLUSH MOUNT FUTUREWEDGE BARRIER	SIZE: B	REV:
THIRD ANGLE PROJECTION		CHECKED: AA	DATE: 3/19/2020	DWG NO: SUFUM-3610-A-1000 GA	WEIGHT:
		APVD:	VERSION:	SCALE: 1:36	SHEET 1 OF 2

GENERAL NOTES:

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURER'S SPECIFICATIONS.
2. CRASH RATING 15000LB (6800KG) @ 50MPH (80KPH) M50
3. REBAR REQUIRED: 933LB PER BARRIER
4. 10FT BARRIER SHOWN. BARRIER IS ALSO AVAILABLE IN 12FT AND 14 FT WIDTHS.

DRAINAGE NOTES:

5. CONTRACTOR TO FIELD VERIFY THE LENGTH, SLOPE, AND FITTING ENGAGEMENT OF EACH LENGTH OF PIPE.
6. ALL FLEXIBLE CONNECTIONS MUST BE RATED FOR CONCRETE.
7. PER INTERNATIONAL PLUMBING CODE, 1° SLOPE MINIMUM REQUIRED ON ALL DRAINAGE OUTLET CHANNELS. SITE SPECIFIED SLOPE AND HEAD DIAMETER TO BE DETERMINING BY NOMINAL RAIN RATE IN ACCORDANCE WITH IPC STORM DRAINAGE REFERENCE.

CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED		 <p>SecureUSA, Inc. 1649 NW 136th Ave. Sunrise, FL 33323 Toll Free: 888.222.4559 www.SecureUSA.net</p>			
<p>TOLERANCES UNLESS OTHERWISE SPECIFIED</p> <p>DIMENSIONS ARE: INCHES</p> <p>X/X ±1/16 X ±0.1 XX ±0.02 XXX ±0.005</p> <p>ANGLE ±30MIN BREAK ALL SHARP EDGES DO NOT SCALE DRAWING</p>					
THIRD ANGLE PROJECTION		DRAWN BY	AD	DESCRIPTION	
		CHECKED	AA		
		APVD			
		MATERIAL		<p>36" 12' K12 FLUSH MOUNT FUTUREWEDGE BARRIER</p>	
		FINISH	AS PER P.O.		
		DATE	3/19/2020	SIZE	B
		VERSION		DWG NO	SUFM-3610-A-1000 GA
				REV	
				SCALE: 1:36	WEIGHT:
				SHEET 2 OF 2	

PROPRIETARY AND CONFIDENTIAL
THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING, ASSUMES CUSTODY THEREOF AND UNDER THE ABOVE TERMS AGREES NOT TO ALLOW USE BY UNAUTHORIZED PERSONS.
©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)

PATH: C:\Users\adodson\Documents\3610 drainage\