



- NOTES:**
1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURES SPECIFICATIONS.
 2. CRASH RATING: 15000LB (6800KG) @ 50MPH (80KM) M50
 3. REBAR REQUIRED: 1048LB
 4. 12 FT BARRIER SHOWN. BARRIER IS ALSO AVAILABLE IN 10 FT, 14 FT AND 16 FT WIDTHS

PROPRIETARY AND CONFIDENTIAL
 THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING, ASSUMES CUSTODY THEREOF AND UNDER THE ABOVE TERMS AGREES NOT TO ALLOW USE BY UNAUTHORIZED PERSONS.
 ©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)

PATH: Z:\Product Drawing Files\Flush Mount Barrier\GENERAL ARRANGEMENTS\

CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED		 SecureUSA, Inc. 4250 Keith Bridge Road Cumming, GA 30041 Toll Free: 888.222.4559/Facsimile: 770.889.7939 www.SecureUSA.net	
TOLERANCES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: INCHES X/X ±1/16 X ±0.05 XX ±0.02 XXX ±0.01 XXXX ±0.001 ANGLE ±30MIN BREAK ALL SHARP EDGES DO NOT SCALE DRAWING THIRD ANGLE PROJECTION			
		MATERIAL: FINISH: DATE: 3/25/2011	SIZE: B DWG NO: SHF3612S-12 REV:
		SCALE: 1:48 WEIGHT: 5942.39	SHEET 1 OF 1