



- NOTE:**
1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.
 2. OPTIONAL GATE ARM AVAILABLE ON SAFE OR ATTACK SIDE.
 3. CRASH RATING: 15000LB (6800KG) @ 40MPH (65KM) M40.
 4. REBAR REQUIRED: 270LB.

CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED				SecureUSA, Inc. 1649 NW 136th Ave. Sunrise, FL 33323 Toll Free: 888.222.4559 www.SecureUSA.net	
TOLERANCES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: INCHES X/X ±1/16 X ±0.1 XX ±0.02 XXX ±0.005 ANGLE ±30MIN BREAK ALL SHARP EDGES DO NOT SCALE DRAWING		DRAWN BY AA CHECKED AA APVD		DESCRIPTION 31 IN 8 FT M40 SHALLOW MOUNT FUTUREWEDGE BARRIERS LEFT HAND EXIT	
THIRD ANGLE PROJECTION 		MATERIAL FINISH AS PER P.O. DATE 8/9/2010 VERSION 1.0		SIZE B DWG NO SHS3108-8 LH EXIT SCALE: 1:36 WEIGHT: 3983.84	
PROPRIETARY AND CONFIDENTIAL <small>THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING ASSUMES CUSTODY THEREOF AND UNDER THE PROVISIONS OF THE PATENT RIGHTS AGREEMENT SHALL NOT ALLOW USE BY UNAUTHORIZED PERSONS. ©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)</small>		Resource\SecureUSA Products\Product Drawing Files\Wedge Barriers\31XX\GENERAL ARRANGEMENTS\M40		SHEET 1 OF 1	