



- NOTES:**
1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURER'S SPECIFICATIONS
 2. OPTIONAL GATE ARM AVAILABLE
 3. CRASH RATING 15,000LB (6,800KG) @ 30MPH (50KPH) M30 (K4)
 4. REBAR REQUIRED: 300LB #5

PROPRIETARY AND CONFIDENTIAL
 THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING, ASSUMES CUSTODY THEREOF AND UNDER THE ABOVE TERMS AGREES NOT TO ALLOW USE BY UNAUTHORIZED PERSONS.
 ©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)

PATH: Z:\Product Drawing Files\Surface Mount Barrier\31XX\GENERAL ARRANGEMENTS\M30\

CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
DIMENSIONS ARE: INCHES	
X/X	±1/16
X	±0.05
XX	±0.02
XXX	±0.01
XXXX	±0.001
ANGLE ±30MIN	
BREAK ALL SHARP EDGES	
DO NOT SCALE DRAWING	
THIRD ANGLE PROJECTION	

 SecureUSA Inc.® Perimeter Defense Solutions		SecureUSA, Inc. 4250 Keith Bridge Road Cumming, GA 30041 Toll Free: 888.222.4559/Facsimile: 770.889.7939 www.SecureUSA.net	
		DESCRIPTION 31 IN 12 FT M30 SHALLOW MOUNTED FUTUREWEDGE BARRIER	
DRAWN BY	M.S	SIZE	DWG NO
CHECKED	R.S	B	SHS3112-4 LH GA
APVD		SCALE: 1:36	WEIGHT: 4596.19
MATERIAL			SHEET 1 OF 1
FINISH			
DATE	10/18/2011		