



MODEL NUMBER	BOLLARD HEIGHT "H"	BOLLARD WEIGHT
FX-PU40-36D	2'-11 1/2" (902mm)	146LB
FX-PU40-30D	2'-5 1/2" (749mm)	132LB




FRONT VIEW (ATTACK)



SIDE VIEW

NOTES:

1. CRASH RATING: 5070LB (2299KG) @ 40MPH (65KPH) PU40
2. CRASH RATING BASED ON 2 BOLLARD HIT & MINIMUM FOUNDATION LENGTH OF 8'-6"
3. REBAR REQUIRED IS APPROXIMATELY 95LB (43KG) PER BOLLARD
4. INSTALLATION MUST BE COMPLETED IN ACCORDANCE WITH MANUFACTURE'S SPECIFICATIONS
5. OPTIONAL DECORATIVE SLEEVE NOT SHOWN
6. BOLLARDS ARE CONCRETE FILLED
7. ALL EXPOSED METAL IS PAINTED WITH BarrierKOTE CORROSION RESISTANT COATING

CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED		 SecureUSA, Inc. 4250 Keith Bridge Road Cumming, GA 30041 Toll Free: 888.222.4559/Facsimile: 770.889.7939 www.SecureUSA.net					
TOLERANCES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: INCHES X/X ±1/16 X ±0.05 XX ±0.02 XXX ±0.01 XXXX ±0.001 ANGLE ±30MIN BREAK ALL SHARP EDGES DO NOT SCALE DRAWING THIRD ANGLE PROJECTION				DESCRIPTION PU40 DECORATIVE FIXED BOLLARD GENERAL ARRANGEMENT			
DRAWN BY	R.STATON	SIZE	B	DWG NO	FX-PU40-D-GA	REV	
CHECKED	MLM	SCALE: 1:18		WEIGHT: 12189.5812189.58		SHEET 1 OF 1	
APVD							
MATERIAL							
FINISH							
DATE	8/23/2011						

PROPRIETARY AND CONFIDENTIAL
 THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING, ASSUMES CUSTODY THEREOF AND UNDER THE ABOVE TERMS AGREES NOT TO ALLOW USE BY UNAUTHORIZED PERSONS.
 ©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)

PATH: C:\GUARDIAR\Products\USA\SUSA Product Drawing Files\Sentry Fixed Bollards\FX-PU40-D3X\CAD\