

## DORMA BTS 80 FLOOR CLOSER

### TECHNICAL DETAILS

- HANDING - DOUBLE ACTING
- PIVOTING - 3/4" OFFSET, 1 1/2" OFFSET and CENTRE LINE
- HOLD OPEN - MULTI-POINT, ADJUSTABLE BETWEEN APPROXIMATELY 75° and 180°
- BACKCHECK - MECHANICAL at APPROXIMATELY 85° and 165°
- DUTY - SPRING SIZE 2 (std) 26 ft-lbs (380 N/m) : MEDIUM SPRING
  - 1 (opt) 11 ft-lbs (160 N/m) : LIGHT SPRING
  - 3 (opt) 39 ft-lbs (570 N/m) : HEAVY SPRING
- SPINDLES - FIELD INTERCHANGEABLE, 5/16" to 2 5/16" DOOR CLEARANCE and 3° OFFSET on SOME SIZES
- DOOR WEIGHT - UP TO 660 lbs (300 kg) in INTERIOR APPLICATION; 54" WIDE (TOP and BOTTOM RAIL) CENTRE HUNG ONLY
- COVER PLATES - BRUSHED or MIRROR STAINLESS STEEL  
BRASS and BRONZE to SPECIAL ORDER

